

# PRODUCT END-OF-LIFE (EOL)

Vertiv™ Geist™ Rack PDUs



## OVERVIEW

### Models:

BRD/L/SVR/VRT/VRTD Series

### Effective Date:

July 31, 2019

## Vertiv Geist Rack PDUs

Effective July 31, 2019, in an effort to streamline the Vertiv Geist Rack PDU (rPDU) offering the following product series will be discontinued.

- BRD
- L
- SVR
- VRT
- VRTD

A detailed list of the affected products and the available replacement model (if applicable) is provided below.

In addition, all standard models across the entire product offering with a 15ft cord length will be reclassified as Configure-to-Order (CTO). Please contact your Vertiv Geist sales representative for purchase information on cord length changes on any standard model.

Vertiv will continue to provide existing customers with support and technical assistance on a reasonable commercial basis after final sale. The standard warranty remains in effect for products covered in this notice.

## Product Series: BRD

Replacement models include hydraulic magnetic circuit breakers.

MODEL #	REPLACEMENT MODEL	VARIATION
BRD120-1036TL	XPR120-103D20TL5	
BRDN120-1036TL	XPR120-103D20TL5	
BRDN080-1034TL	XPR120-103D20TL5	(12) Outlet
BRD120-1536TL	XPR120-103D20TL5	10ft / 3m cord
BRDN120-1536TL	XPR120-103D20TL5	10ft / 3m cord
BRDN080-1534TL	XPR120-103D20TL5	(12) Outlet, 10ft / 3m cord
BRDAN080-1034TL	XPRA120-103D20TL5	(12) Outlet
BRDAN080-1534TL	XPRA120-103D20TL5	10ft / 3m cord
BRDCN080-1034TL	XPRC120-103D20TL5	(12) Outlet
BRDCN080-1534TL	XPRC120-103D20TL5	10ft / 3m cord

## Product Series: L

MODEL #	REPLACEMENT MODEL	VARIATION
GLCE-002C19-00C20	Not Available	
GLCE-001C13-00C14	Not Available	
LCE-002C19-00C20	Not Available	
LCE-001C13-00C14	Not Available	

## Product Series: VRTD

Replacement models include hydraulic magnetic circuit breakers

MODEL #	REPLACEMENT MODEL	VARIATION
VRTDN200-10310TL	XPB240-103D20TL5	
VRTDAN200-10310TL	I10055	Upgradeable
VRTDCN200-10310TL	I10055	Upgradeable

Product Series: SVR

MODEL #	REPLACEMENT MODEL	VARIATION
SVRA104-10	VSSA104-101S15	
SVRA104-1025	VSSA104-102S20	
SVRA104-1025TL	VSSA104-102S20TL	
SVRA104-15	VSSA104-101S15	10ft / 3m cord
SVRA104-1525	VSSA104-102S20	10ft / 3m cord
SVRA104-1525TL	VSSA104-102S20TL	10ft / 3m cord
SVRAA104-10	Not Available	
SVRAA104-1025	Not Available	
SVRAA104-1025TL	Not Available	
SVRAAN104-10	Not Available	
SVRAAN104-1025	Not Available	
SVRAAN104-1025TL	Not Available	
SVRAC104-10	Not Available	
SVRAC104-1025	Not Available	
SVRAC104-1025TL	Not Available	
SVRACN104-10	Not Available	
SVRACN104-1025	Not Available	
SVRACN104-1025TL	Not Available	
SVRAN104-10	VSSAN104-101S15	
SVRAN104-1025	VSSAN104-102S20	
SVRAN104-1025TL	VSSAN104-102S20TL	
SVRAN104-15	VSSAN104-101S15	10ft / 3m cord
SVRAN104-1525	VSSAN104-102S20	10ft / 3m cord
SVRAN104-1525TL	VSSAN104-102S20TL	10ft / 3m cord
SVRB204-10	VSSB204-101S15	
SVRB204-10210	VSSB204-102S20	
SVRB204-10210TL	VSSB204-102S20TL	
SVRB204-15	VSSB204-101S15	10ft / 3m cord
SVRB204-15210	VSSB204-102S20	10ft / 3m cord
SVRB204-15210TL	VSSB204-102S20TL	10ft / 3m cord
SVRBA204-10	VSSBA204-101S15	
SVRBA204-10210	VSSBA204-102S20	
SVRBA204-10210TL	VSSBA204-102S20TL	
SVRBAN204-10	VSSBAN204-101S15	
SVRBAN204-10210	VSSBAN204-102S20	
SVRBAN204-10210TL	VSSBAN204-102S20TL	
SVRBC204-10	VSSBC204-101S15	
SVRBC204-10210	VSSBCN204-102S20	No Switch
SVRBC204-10210TL	VSSBCN204-102S20TL	No Switch
SVRBCN204-10	VSSBCN204-101S15	
SVRBCN204-10210	VSSBCN204-102S20	
SVRBCN204-10210TL	VSSBCN204-102S20TL	

MODEL #	REPLACEMENT MODEL	VARIATION
SVRBN204-10	VSSBN204-101S15	
SVRBN204-10210	VSSBN204-102S20	
SVRBN204-10210TL	VSSBN204-102S20TL	
SVRBN204-15	VSSBN204-101S15	10ft / 3m cord
SVRBN204-15210	VSSBN204-102S20	10ft / 3m cord
SVRBN204-15210TL	VSSBN204-102S20TL	10ft / 3m cord
SVRC144-10	VSSC144-101S15	
SVRC144-1027	VSSC144-102S20	
SVRC144-1027TL	VSSC144-102S20TL	
SVRC144-15	VSSC144-101S15	10ft / 3m cord
SVRC144-1527	VSSC144-102S20	10ft / 3m cord
SVRC144-1527TL	VSSC144-102S20TL	10ft / 3m cord
SVRCA144-10	Not Available	
SVRCA144-1027	Not Available	
SVRCA144-1027TL	Not Available	
SVRCAN144-10	Not Available	
SVRCAN144-1027	Not Available	
SVRCAN144-1027TL	Not Available	
SVRCC144-10	Not Available	
SVRCC144-1027	Not Available	
SVRCC144-1027TL	Not Available	
SVRCCN144-10	Not Available	
SVRCCN144-1027	Not Available	
SVRCCN144-1027TL	Not Available	
SVRCN144-10	Not Available	
SVRCN144-1027	VSSCN144-102S20	
SVRCN144-1027TL	VSSCN144-102S20TL	
SVRCN144-15	Not Available	
SVRCN144-1527	VSSCN144-102S20	10ft / 3m Cord
SVRCN144-1527TL	VSSCN144-102S20TL	10ft / 3m Cord
SVRL064-10	VSSL084-101R15	8 Outlet
SVRL064-1023	VSSL084-102S20	8 Outlet
SVRL064-1023TL	VSSL084-102S20TL	8 Outlet
SVRL064-15	VSSL084-101R15	8 Outlet, 10ft / 3m cord
SVRL064-1523	VSSL084-102S20	8 Outlet, 10ft / 3m Cord
SVRL064-1523TL	VSSL084-102S20TL	8 Outlet, 10ft / 3m Cord
SVRLN064-10	VSSLN084-101R15	8 Outlet
SVRLN064-1023	VSSLN084-102S20	8 Outlet
SVRLN064-1023TL	VSSLN084-102S20TL	8 Outlet
SVRLN064-15	VSSLN084-101R15	8 Outlet, 10ft / 3m cord
SVRLN064-1523	VSSLN084-102S20	8 Outlet, 10ft / 3m Cord
SVRLN064-1523TL	VSSLN084-102S20TL	8 Outlet, 10ft / 3m Cord

Product Series: VRT

MODEL #	REPLACEMENT MODEL	VARIATION
VRTA100-10	NSVA100-101S15	
VRTA100-1025	NSVA100-102S20	
VRTA100-1025TL	NSVA100-102S20TL	
VRTA100-15	NSVA100-101S15	10ft / 3m cord
VRTA100-1525	NSVA100-102S20	10ft / 3m cord
VRTA100-1525TL	Not Available	
VRTAA100-10	Not Available	
VRTAA100-1025	Not Available	
VRTAA100-1025TL	Not Available	
VRTAAN100-10	Not Available	
VRTAAN100-1025	Not Available	
VRTAAN100-1025TL	Not Available	
VRTAC100-10	Not Available	
VRTAC100-1025	Not Available	
VRTAC100-1025TL	Not Available	
VRTACN100-10	Not Available	
VRTACN100-1025	Not Available	
VRTACN100-1025TL	Not Available	
VRTAN100-10	NSVAN100-101S15	
VRTAN100-1025	NSVAN100-102S20	
VRTAN100-1025TL	NSVAN100-102S20TL	
VRTAN100-15	NSVAN100-101S15	10ft / 3m Cord
VRTAN100-1525	NSVAN100-102S20	10ft / 3m cord
VRTAN100-1525TL	NSVAN100-102S20TL	10ft / 3m Cord
VRTB200-10	NSVB200-101S15	
VRTB200-10210	NSVB200-102S20	
VRTB200-10210TL	NSVB200-102S20TL	
VRTB200-15	NSVB200-101S15	10ft / 3m Cord
VRTB200-15210	NSVB200-102S20	10ft / 3m Cord
VRTB200-15210TL	NSVB200-102S20TL	10ft / 3m Cord
VRTBA200-10	NSVBA200-101S15	
VRTBA200-10210	NSVBA200-102S20	
VRTBA200-10210TL	NSVBA200-102S20TL	
VRTBAN200-10	NSVBAN200-101S15	
VRTBAN200-10210	NSVBAN200-102S20	
VRTBAN200-10210TL	NSVBAN200-102S20TL	
VRTBC200-10	NSVBC200-101S15	
VRTBC200-10210	NSVBC200-102S20	
VRTBC200-10210TL	NSVBC200-102S20TL	
VRTBCN200-10	NSVBCN200-101S15	
VRTBCN200-10210	NSVBCN200-102S20	
VRTBCN200-10210TL	NSVBCN200-102S20TL	

MODEL #	REPLACEMENT MODEL	VARIATION
VRTBN200-10	NSVBN200-101S15	
VRTBN200-10210	NSVBN200-102S20	
VRTBN200-10210TL	NSVBN200-102S20TL	
VRTBN200-15	NSVBN200-101S15	10ft / 3m Cord
VRTBN200-15210	NSVBN200-102S20	10ft / 3m Cord
VRTBN200-15210TL	NSVBN200-102S20TL	10ft / 3m Cord
VRTC140-10	Not Available	
VRTC140-1027	Not Available	
VRTC140-1027TL	Not Available	
VRTC140-15	Not Available	
VRTC140-1527	Not Available	
VRTC140-1527TL	Not Available	
VRTCA140-10	Not Available	
VRTCA140-1027	Not Available	
VRTCA140-1027TL	Not Available	
VRTCAN140-10	Not Available	
VRTCAN140-1027	Not Available	
VRTCAN140-1027TL	Not Available	
VRTCC140-10	Not Available	
VRTCC140-1027	Not Available	
VRTCC140-1027TL	Not Available	
VRTCCN140-10	Not Available	
VRTCCN140-1027	Not Available	
VRTCCN140-1027TL	Not Available	
VRTCN140-10	Not Available	
VRTCN140-1027	Not Available	
VRTCN140-1027TL	Not Available	
VRTCN140-15	Not Available	
VRTCN140-1527	Not Available	
VRTCN140-1527TL	Not Available	
VRTL060-10	NSVL080-101R15	8 Outlet
VRTL060-1023	NSVL080-102S20	8 Outlet
VRTL060-1023TL	NSVL080-102S20TL	
VRTL060-15	NSVL080-101R15	8 Outlet, 10ft / 3m Cord
VRTL060-1523	NSVL080-102S20	8 Outlet, 10ft / 3m Cord
VRTL060-1523TL	NSVL080-102S20TL	8 Outlet, 10ft / 3m Cord
VRTLN060-10	NSVLN080-101R15	8 Outlet
VRTLN060-1023	NSVLN080-102S20	8 Outlet
VRTLN060-1023TL	NSVLN080-102S20TL	
VRTLN060-15	NSVLN080-101R15	8 Outlet, 10ft / 3m Cord
VRTLN060-1523	NSVLN080-102S20	8 Outlet, 10ft / 3m Cord
VRTLN060-1523TL	NSVLN080-102S20TL	8 Outlet, 10ft / 3m Cord

Vertiv.com | Vertiv Headquarters, 1050 Dearborn Drive, Columbus, OH, 43085, USA

© 2019 Vertiv Group Corp. All rights reserved. Vertiv™ and the Vertiv logo are trademarks or registered trademarks of Vertiv Group Corp. While every precaution has been taken to ensure accuracy and completeness herein, Vertiv Group Corp. assumes no responsibility, and disclaims all liability, for damages resulting from use of this information or for any errors or omissions. Specifications are subject to change without notice.