


- ① OFF/ENTER BUTTON
- ② SELECT BUTTON
- ③ ON/MUTE BUTTON
- ④ INPUT POWER CORD: NEMA 5-15P WITH 6 FOOT ATTACHED CORD
- ⑤ 16A INPUT CIRCUIT BREAKER
- ⑥ USB PORT
- ⑦ EPO CONNECTOR
- ⑧ RJ11/RJ-45 DATA LINE CONNECTORS
- ⑨ INTELLISLOT PORT. NETWORK COMMUNICATIONS CARD OPTIONAL
- ⑩ OUTPUT RECEPTACLES: 3 NEMA 5-15R ALWAYS ON
- ⑪ OUTPUT RECEPTACLES: 3 NEMA 5-15R PROGRAMMABLE GROUP



NOTES:

1. UNIT DIMENSIONS: 6.2" x 15.6" x 8.7" (158mm) x (397mm) x (220mm)
2. UNIT WEIGHT: 28LBS (12.7KG)
3. SHIPPING DIMENSIONS: 9.1" x 19.5" x 12.8" (230mm) x (495mm) x (325mm)
4. SHIPPING WEIGHT: 31.3LBS (14.2KG)
5. MINIMUM AIRFLOW CLEARANCE IS 4.0" (100.0mm) - FRONT/REAR/SIDE
6. ALL SITE WIRING IS TO BE IN COMPLIANCE WITH NATIONAL AND LOCAL ELECTRIC CODES
7. UNIT INPUT: 100~125 VAC, 60/50HZ, 10A
8. UNIT OUTPUT: 100/110/115/120/125VAC, 60/50HZ, 1500VA/1350W, 12A, @125VAC INPUT OR 1440VA/1350W, 12A, @120VAC INPUT OR 1380VA/1350W, 12A, @115VAC INPUT OR 1275VA/1147W, 11.6A, @110VAC INPUT OR 1200VA/1147W, 12A, @100VAC INPUT

DRAWN BY B. LAY CHK BY N. SECORD REF. DWG.	SHEET NO. 1 OF 1	PSI5-1500MT120LI	DWG. NO. PSI5-1500MT120LI	DATE 10/9/20	REV. # 0	1050 DEARBORN DRIVE P.O. BOX 29186 COLUMBUS, OHIO 43229	
	ECN NO.						