

OVERVIEW

Upgradeable Unit Level EC Monitored rPDUs provide reliable power distribution to critical IT equipment while delivering a comprehensive view of input level power usage via remote network access. Includes environmental monitoring capabilities to obtain realtime environmental metrics. Upgrade the hot-swappable monitoring device on select units to leverage new technologies and accommodate changing business needs.

Benefits

- Reliable power distribution with local and remote power monitoring options offer quick access to critical power usage information to evaluate energy usage trends and maximize uptime.
- **Environmental monitoring** capabilities with the addition of optional environmental sensors ensure users have critical infrastructure data at their fingertips to prevent climate-related equipment failure and system downtime.
- Fault-Tolerant Daisy Chaining with RSTP simplifies intelligent rPDU connectivity and ensures data is reported even when a breakin the network chain occurs. Supports up to 40 rPDUs.
- Every unit is 100% tested for reliability and functionality.

Part #: UI30006L

Model Number: DU03E4W1-36PNB7-1S02A9K00-S-A

Category: Monitored

Sub Category: Unit Level EC

Power Configuration: Variable, Variable, 11.0kW Physical Configuration: 70in / 1778mm, Vertical

Product Summary: rPDU, Monitored Unit Level EC, 11.0kW, Variable Power Configuration, Vertical, (24)

Locking IEC C13, (12) Locking IEC C19, Universal Inlet, Black Powder Coat.

Monitoring: Input and per Phase power monitoring with Circuit/Breaker current monitoring.

Environmental monitoring via optional remote sensors. Daisy chain Ethernet

connectivity. Local high visibility LED display.

Plug Form: Receptacle:



Universal Inlet







Locking IEC C13 (Quantity: 24)

Locking IEC C19 (Quantity: 12)

Chassis Color Options:



To discuss color options, contact your local sales representative.

Product Specification and Options

System Features

Monitoring	Input and per Phase power monitoring with Circuit/Breaker current monitoring. Environmental monitoring via optional remote sensors. Daisy chain Ethernet connectivity. Local high visibility LED display.
Input Monitoring	Total Unit Monitoring (kWh, W, VA, PF) Phase Monitoring (kWh, W, VA, PF, V, A)
	Power Measurements Compliant with ANSI C12.1 and IEC 62053 21 at 1% Accuracy Class Requirements
Quantity Of Inputs	1
Maximum Input Power (Defined by Facility Side Cable)	48A Single Phase, 240V Max, 11.0kW 24A 3 Phase DELTA, 240V Max, 8.6kW 16A Three Phase WYE, 240/415V Max, 11.0kW
Frequency	50/60Hz
Over Current Protection	(3) 16A Double Pole Magnetic Breakers (10kAIC Rated)
Switch	Breaker/Switch Combination
Scrolling / Rotatable Digital Display	Yes
Power Entry Location	Pivoting Connector
Plug Type	Universal Inlet
Combined Total Receptacle/Socket Quantity	36
Alternating Phase/Circuits	Yes
Receptacle/Socket Type #1	U-Lock IEC C13
- Quantity on Face	24
- Quantity per Breaker	8
- U-Lock Color ID	3 Circuit = Orange, Green, Blue
- Style	Individual
- Voltage per Receptacle/Socket	Defined by Facility Side Cable
Receptacle/Socket Type #2	U-Lock IEC C19
- Quantity on Face	12
- Quantity per Breaker	4
- U-Lock Color ID	3 Circuit = Orange, Green, Blue
- Style	Individual
- Voltage per Receptacle/Socket	Defined by Facility Side Cable
Internal RMS Voltage Sensor	Yes
Internal RMS Current Sensor	Yes
Network Connection	Dual 10/100/1000Mbps Ethernet
Protocols Supported	DHCP, HTTP, HTTPS, IPv4, IPv6, LDAP, NTP, RADIUS, RSTP, SSH, SMTP, SNMP (v1/v2c/v3), Syslog, TACACS+
Data Access Formats	CSV datalog, JSON API, JSON datalog
USB Support	Yes
IP Reset Button	Yes
Hard Reboot Button	Yes
Serial Connection	RS232 via RJ45
Remote Sensor RJ Connection Jacks	1 (Supports up to 16 Sensors)
Maximum Operating Temperature	60C / 140F

Configuration	Zero U
Toolless Mounting Hardware - Center to Center Spacing	61.25in and 64.75in / 1556mm and 1645mm
Product Warranty	5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years
Certification/Agency Approvals	CE Marked
Certification/Agency Approvals	Complies with EN 55032 and EN 55035
Certification/Agency Approvals	FCC Part 15 Class A Conformance
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	RCM Mark (EMC Only)
Certification/Agency Approvals	Complies with IEC 62368-1 (DOC Available)
Certification/Agency Approvals	UL & c-UL Listed 62368-1
Certification/Agency Approvals	China RoHS
Certification/Agency Approvals	C _o Mark
Chassis Dimensions (LxWxD)	70in x 2in x 2.25in / 1778mm x 51mm x 58mm
Doghouse (D)	1.4in / 36mm
Shipped Weight	22lbs (9.98kg)